## **BED FRAMES LOW BED 100 MAX**



## **LOW BED 100 MAX**

The Low Bed 100 MAX is truly universal because the bed frame can be used with most other manufacturers bed ends, old and new. The transition box mounted on the foot section is key to interchangeability. The transition box allows you to change the rotation of the high-low shaft.



## **Key Product Features**

- Headboard is taller than footboard to better fit home decor.
- The wood grain panels are break and scratch resistant.
- Once installed, the high/low shaft will stay with the bed to eliminate loss or forgetting on future installations.
- Labels and color-coded springs assure accurate installation of side rails for patient safety.
- Unique motor is completely self-contained to reduce weight and noise.
- 9 1/2" to 23 1/2" deck height.
- Easy to set up.
- Top mounted Hi/Lo crank accessibility.
- 450 lb. weight capacity.
- Height adjustable motor comes pre-installed on the foot section.

- Caster easily moves from standard to low bed position.
- The motor assembly can be installed and removed with patient in bed.
- The motor is UL approved.
- In the event of a power failure, a 9 volt battery, located in the motor, can lower the head and foot sections nine times.
- New and improved hand pendant has large, easy to use controls.
- Bed ships in two cartons.
- Channel frame construction provides superior strength and reduced weight.
- Zinc coated spring deck.
- Warranty: (Original purchaser) 5 years on motor and hand control, Limited Lifetime on welds and frame, 1 year on all other parts and components.

